# Ultraflow XF800



#### EXCEPTIONAL RELIABILITY AND PRODUCT RANGE WITH CONSISTENT, FAST CHANGEOVERS

#### **KEY ADVANTAGES**

- Continuous motion design
- Motorized adjustments with digital feedback and calculated positions for fast initial pack setup
- Changeover wizard provides onscreen instructions during changeover
- Compliant materials for wide operating window and variations to incoming product
- Large format range
- Limited change parts
- Closed loop film tension control
- Potential film savings with small panels and thinner films
- Flexible layout options and motorized lap seal for left and right film panels
- Fast response lap seal heater: Benefits include better pack quality, energy and film savings, and faster ramp-up rates
- LED indicators for timed air

### **MAJOR OPTIONS**

- 5th infeed lane and 3rd level
- Tipped / Turned roll detect system for infeed conveyor
- 2nd perforator

## SPECIFICATIONS

r	
Infeed lanes	4 (5th lane optional)
Levels	2 (3rd level optional)
Package dimensions	Length: 7" – 24" (178 - 610 mm) Width: 3.5" – 25" (89 - 635 mm) Height: 3.5" – 15" (89 - 381 mm)
Incoming roll dimensions	Length: 3.5" – 13.5" (89 – 343 mm) Diameter: 3.5" – 7" (89 – 178 mm)
Film roll dimensions	Width: up to 80" (up to 2032 mm) Diameter: up to 40" (up to 1016 mm) Film guage: 0.7 - 1.5 mil (18 - 38 µm)
Pack speeds*	Single or 2-pack towel/4-pack tissue: 200 PPM 9-pack tissue: 110 PPM (up to 130 below 4.5" dia.) 12-pack tissue (2 level): 65 PPM 8-pack towel (2 level): 50 PPM 12-pack towel (3 high) 40 PPM
Changeover times	30-40 min. typically "Good pack to good pack" Step-by-step on-screen instructions

\* Speeds listed are those which can be achieved 24/7. Guaranteed machine rate for each package format is determined after review of the actual product by PCMC



